



Uchwyt do wkładania/wyjmowania typu IEL, czarna dźwignia, szary przycisk, Góra, 100 sztuk



NUMER KATALOGOWY

20817-685

Uchwyt wkładki/ściągnacz, typ IEL zgodnie z normą IEEE 1101.10. Przesunięcie 0,1" dwa z tych uchwytów mogą pokonać siłę pojedynczej dźwigni 700N (na parę).

FUNKCJE

Nadaje się do sił wkładania i wyciągania do 700 N (na parę)

Zgodnie z normami IEEE 1101.10 i IEC 60297-3-102

Można zamontować mikroprzełącznik

Offset 0.1" jest używany dla zasilaczy z SMD Plus



ATRYBUTY PRODUKTU

Liczba opakowań: 100

Typ uchwytu: IEL; Górny przedni

Klasyfikacja palności: UL® 94V-0

Kolor: Czarny

Zgodność z: EN 45545-2

Materiał: Poliwęglan; Stop cynku

Typ produktu: Uchwyt

Typ: Przyrząd do wsuwania/wyciągania, przesunięcie 0,1"

Współpracuje z: Panele przednie

Waga brutto: 2.384kg


*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address,

parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

DODATKOWE INFORMACJE O PRODUKCIE

Kółki kodowania i mikroprzełącznik należy zamówić oddzielnie.

SCHEMATY



OSTRZEŻENIE

Produkty nVent powinny być instalowane i używane wyłącznie zgodnie z instrukcjami i materiałami szkoleniowymi nVent. Instrukcje są dostępne na stronie www.nvent.com oraz u przedstawiciela działu obsługi klienta firmy nVent. Nieprawidłowa instalacja, niewłaściwe użycie, niewłaściwe zastosowanie lub inne nieprzestrzeganie instrukcji i ostrzeżeń nVent może spowodować nieprawidłowe działanie produktu, uszkodzenie mienia, poważne obrażenia ciała i śmierć i/lub utratę gwarancji.

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff



Marki w naszej ofercie:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE