


Zestaw modułu wtykowego do PMC z uchwytem IEL czarny, ekranowany panel przedni w kształcie litery U (tekstylny), 3 U, 4 km



NUMER KATALOGOWY

20836-460

Panel przedni w kształcie litery U z wycięciem dla PMC.
Osłona do tekstylnej uszczelki EMC.

FUNKCJE

Zgodnie z normą IEEE P1386, karta PCI Mezzanine

Dla pojedynczych modułów 69.0 x 76.5 mm lub
podwójnych 139.0 x 76.5 mm

Dla standardowych modułów we/wy mezzanie, które łączą się z kartami nośnymi

PMC = Karta PCI Mezzanine

FPGA = programowalna macierz bramek polowych

Panel przedni z profilem U 3 U, 4 km, z uszczelnieniem tekstylnym

Ekranowanie EMC dla panelu przedniego i pokrycia dla wycięć na panelu przednim

ATRYBUTY PRODUKTU

Wysokość stojaka: 3U

Liczba opakowań: 1

Typ uchwyty: IEL

Montaż: Przykręcany przód

Typ uszczelki: Tekstylna

Wykończenie z przodu: Anodyzowany

Wykończenie z tyłu: Przewodzące

Zgodność z: PMC Mezzanine, IEEE P1386

Ekranowanie EMC: Tak

Wykończenie: Anodyzowany; Powierzchnia pasywowana

Materiał: Aluminium

Typ produktu: Panel przedni

Szerokość stojaka: 4HP

Typ: Panel przedni z uchwytem (PIU)

Waga netto: 0.088kg

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

OSTRZEŻENIE

Produkty nVent powinny być instalowane i używane wyłącznie zgodnie z instrukcjami i materiałami szkoleniowymi nVent. Instrukcje są dostępne na stronie www.nvent.com oraz u przedstawiciela działu obsługi klienta firmy nVent. Nieprawidłowa instalacja, niewłaściwe użycie, niewłaściwe zastosowanie lub inne nieprzestrzeganie instrukcji i ostrzeżeń nVent może spowodować nieprawidłowe działanie produktu, uszkodzenie mienia, poważne obrażenia ciała i śmierć i/lub utratę gwarancji.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Marki w naszej ofercie:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE