

Zestaw panelu przedniego, ekranowany, na zawiasach dolny, 6 U, 84 HP, 2.5 mm, Al, z przodu anodyzowany, z tyłu przewodzący

NUMER KATALOGOWY

20848-604

Dolny panel przedni z profilem U na zawiasach dla uszczelki tekstylnej.


FUNKCJE

Panel przedni z profilem U można odzepić pod kątem otwarcia 135° (nie RatiopacPRO)

Umożliwia montaż na szynach poziomych

Ekranowany panel przedni U z tekstylną uszczelką EMC

Nadaje się do podstawek (EuropacPRO) i skrzynek (RatiopacPRO, PropacPRO, CompacPRO)



ATRYBUTY PRODUKTU

Wysokość stojaka: 6U

Typ akcesorium: Panel przedni

Szerokość stojaka: 84HP

Liczba opakowań: 1

Montaż: Na zawiasach, na dole

Typ uszczelki: Tekstylia

Wykończenie z przodu: Anodyzowany

Wykończenie z tyłu: Przewodzące

Obrabiane krawędzie: Nie

Zgodność z: IEC 60297-3-101; IEEE 1101.1/10

Głębokość (D): 2.5mm

Ekranowanie EMC: Nie (możliwość modernizacji)

Wykończenie: Anodyzowany; Powierzchnia pasywowana

Wysokość (H): 261.8mm

Materiał: Aluminium

Typ produktu: Panel przedni

Typ: Panel przedni bez uchwytu

Szerokość (W): 426.4mm


Waga netto: 1kg

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

DODATKOWE INFORMACJE O PRODUKCIE

Panel przedni można zdjąć w położeniu otwarcia ($> 135^\circ$).

SCHEMATY



OSTRZEŻENIE

Produkty nVent powinny być instalowane i używane wyłącznie zgodnie z instrukcjami i materiałami szkoleniowymi nVent. Instrukcje są dostępne na stronie www.nvent.com oraz u przedstawiciela działu obsługi klienta firmy nVent. Nieprawidłowa instalacja, niewłaściwe użycie, niewłaściwe zastosowanie lub inne nieprzestrzeganie instrukcji i ostrzeżeń nVent może spowodować nieprawidłowe działanie produktu, uszkodzenie mienia, poważne obrażenia ciała i śmierć i/lub utratę gwarancji.

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff



Marki w naszej ofercie:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE