


Zestaw modułu wtykowego z uchwytem IEL do tylnego wejścia/wyjścia, ekranowany, czarny, 3 U, 4 km



NUMER KATALOGOWY

20848-751

Moduł wtykowy, z czarnym uchwytem wkładki/ściągacza IEL, 3 U, tylny zespół we/wy. Przedni panel w kształcie litery U umożliwia ekranowanie za pomocą tekstylnej uszczelki.

FUNKCJE

Przedni panel w kształcie litery U do uszczelnienia tekstylnego

Nadaje się do sił wkładania i wyciągania do 700 N (na parę)

Włącz instalację mikroprzełącznika

Włącz instalację koderów zgodnie z normą IEC 60297-3-103/ IEEE 1101.10



ATRYBUTY PRODUKTU

Szerokość stojaka: 4HP

Liczba opakowań: 1

Typ uchwyty: IEL

Montaż: Przykręcane tylne We/Wy

Typ uszczelki: Tekstylna

Wykończenie z przodu: Anodyzowany

Wykończenie z tyłu: Powierzchnia trawiona

Obrabiane krawędzie: Nie

Zgodność z: IEC 60297-3-102; IEEE 1101.10; IEC 60297-3-103; IEEE 1101.1/11

Ekranowanie EMC: Tak

Wykończenie: Anodyzowany; Powierzchnia pasywowana

Wysokość (H): 128.4mm

Materiał: Aluminium

Typ produktu: Panel przedni

Wysokość stojaka: 3U


Typ: Panel przedni z uchwytem (PIU)

Szerokość (W): 20mm

Waga netto: 0.08kg

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

SCHEMATY



OSTRZEŻENIE

Produkty nVent powinny być instalowane i używane wyłącznie zgodnie z instrukcjami i materiałami szkoleniowymi nVent. Instrukcje są dostępne na stronie www.nvent.com oraz u przedstawiciela działu obsługi klienta firmy nVent. Nieprawidłowa instalacja, niewłaściwe użycie, niewłaściwe zastosowanie lub inne nieprzestrzeganie instrukcji i ostrzeżeń nVent może spowodować nieprawidłowe działanie produktu, uszkodzenie mienia, poważne obrażenia ciała i śmierć i/lub utratę gwarancji.

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff



Marki w naszej ofercie:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE