

Sterownik dla LHX+ 5 KW i 10 KW

NUMER KATALOGOWY

23130-668



Moduł sterujący wzbogaca LHX+. Łączy się z czujnikami LHX+ i zaworem płynu chłodzącego z silnikiem 23130-607. Umożliwia to chłodnicę sterowanie przepływem powietrza chłodzącego w oparciu o wartość zadaną temperatury schłodzonego (zasilania) powietrza. Zapewnia zaawansowane funkcje zdalnego monitorowania i różne funkcje konfiguracyjne.

FUNKCJE

Sterowanie przepływem płynu chłodzącego na podstawie nastawy temperatury schłodzonego (zasilania) powietrza. Więcej funkcji sterowania z pakietem kontroli wody

Oddzielna, kompaktowa jednostka sterująca 19". Bez luźnych przewodów w górnej części szafy

Wyraźnie oznaczone złącza czujnika plug & play

ATRYBUTY PRODUKTU

Wysokość: 88mm

Głębokość: 220mm

Współpracuje z: Varistar; Varistar CP

Liczba opakowań: 1

Kolor: Czarny/szary

Kod koloru: RAL 7021

Wykończenie: Cynkowane aluminium

Napięcie wejściowe AC: 230V

Materiał: Stal

Rodzina produktów: Varistar CP

Typ produktu: Moduł sterujący

Wysokość stojaka: 2U

Szerokość: 439.5mm

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on

SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

DODATKOWE INFORMACJE O PRODUKCIE

Opcjonalny wyświetlacz zewnętrzny.

OSTRZEŻENIE

Produkty nVent powinny być instalowane i używane wyłącznie zgodnie z instrukcjami i materiałami szkoleniowymi nVent. Instrukcje są dostępne na stronie www.nvent.com oraz u przedstawiciela działu obsługi klienta firmy nVent. Nieprawidłowa instalacja, niewłaściwe użycie, niewłaściwe zastosowanie lub inne nieprzestrzeganie instrukcji i ostrzeżeń nVent może spowodować nieprawidłowe działanie produktu, uszkodzenie mienia, poważne obrażenia ciała i śmierć i/lub utratę gwarancji.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Marki w naszej ofercie:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE