


# Klatka do montażu płyty poziomej, 3 U, 20 HP, szyna przednia z długą krawędzią



## NUMER KATALOGOWY

**24564-118**

Klatka na płyty poziome oferuje możliwość wkładania płyt 6 U do podszerek o wysokości 3 lub 4 U lub obudów na pulpit. Dodaj przedni panel, aby pokryć zestaw montażowy.

## FUNKCJE

Do montażu poziomego podwójnych płyt Euroboardowych w 3 lub 4 U wysokich podpór/skrzyń



## ATRYBUTY PRODUKTU

Wysokość stojaka: 3U

Szerokość stojaka: 20HP

Liczba opakowań: 1

Materiał: Aluminium; Stop cynku

Rodzina produktów: EuropacPRO

Typ produktu: Zestaw montażowy

Typ: Montaż na płycie poziomej; Z długą wargą

Współpracuje z: Stojaki podrzędne

Waga netto: 0.791kg

\*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

## DODATKOWE INFORMACJE O PRODUKCIE

Proszę zamówić przednią ramę i materiał ekranujący EMC oddzielnie.

54 wymagane miejsce te.

## OSTRZEŻENIE

Produkty nVent powinny być instalowane i używane wyłącznie zgodnie z instrukcjami i materiałami szkoleniowymi nVent. Instrukcje są dostępne na stronie [www.nvent.com](http://www.nvent.com) oraz u przedstawiciela działu obsługi klienta firmy nVent. Nieprawidłowa instalacja, niewłaściwe użycie, niewłaściwe zastosowanie lub inne nieprzestrzeganie instrukcji i ostrzeżeń nVent może spowodować nieprawidłowe działanie produktu, uszkodzenie mienia, poważne obrażenia ciała i śmierć i/lub utratę gwarancji.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Marki w naszej ofercie:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE