

Płyta rozdzielająca EuropacPRO, 6 U, 160 mm

NUMER KATALOGOWY

34562-763


Płyta rozdzielająca umożliwia użytkownikowi utworzenie oddzielnego obszaru wewnątrz podstacywny lub obudowy. Płytę można przypiąć do perforacji poziomych szyn. Jeśli płyta zostanie zmontowana, podreguły lub skrzynie muszą zostać zdemontowane.

FUNKCJE

Montaż poprzez przypięcie do poziomych szyn

Wymagana ilość miejsca po stronie podzespołu: 2.0 mm

Montaż zależy od sposobu uszczelniania (stal nierdzewna/uszczelka tekstylna)



ATRYBUTY PRODUKTU

Wysokość stojaka: 6U

Liczba opakowań: 1

Głębokość: 160mm

Długość: 160mm

Materiał: Stal nierdzewna

Rodzina produktów: EuropacPRO

Typ produktu: Panel boczny

Współpracuje z: Stojaki podrzędne

Waga netto: 0.27kg

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

DODATKOWE INFORMACJE O PRODUKCIE

Późniejsza instalacja płyty rozdzielającej w zamontowanym podpórcie wymaga wcześniejszego wymontowania przewodnic poziomych.

OSTRZEŻENIE

Produkty nVent powinny być instalowane i używane wyłącznie zgodnie z instrukcjami i materiałami szkoleniowymi nVent. Instrukcje są dostępne na stronie www.nvent.com oraz u przedstawiciela działu obsługi klienta firmy nVent. Nieprawidłowa instalacja, niewłaściwe użycie, niewłaściwe zastosowanie lub inne nieprzestrzeganie instrukcji i ostrzeżeń nVent może spowodować nieprawidłowe działanie produktu, uszkodzenie mienia, poważne obrażenia ciała i śmierć i/lub utratę gwarancji.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Marki w naszej ofercie:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE