

Improved nVent CADDY Cat HP J-Hook with Hammer-On Flange Clip

The Improved nVent CADDY Cat HP J-Hook with Hammer-On Flange Clip is an innovative assembly featuring a combination of the Improved nVent CADDY Cat HP J-Hook with a Hammer-On Flange Clip attachment. This solution attaches easily to beam flanges, and reduces the need for screws and rivets, dramatically reducing installation time and improving productivity. Engineered for high-performance data cable management, this system supports Cat 5e, Cat 6, Cat 6A, Cat 7, and fiber optic cables with superior fill capacity and load ratings compared to most non-continuous alternatives. The Assemblies' rounded edges ensure proper bend radius support, protecting cable integrity and optimizing performance.

CARACTERÍSTICAS

Requires only a hammer to install

Versa-Mount Technology: Innovative attachment design provides multiple structural and installation methods for wall, ceiling, and threaded rod mounting applications

Improved design allows for optimized inventory, reducing job site scheduling risks associated with multiple SKUs

Provides optimal support for high-performance data cable—including category cable, Power over Ethernet (PoE), and fiber optic

Complies with EN 50174-2

Meets ISO®/IEC 14763-2, ANSI®/TIA 568 and ANSI®/TIA 569



ESPECIFICAÇÕES

Table 1/2

Número de catálogo	Número do artigo	Material	Acabamento	Diâmetro	Area	Cable Capacity, Cat 5e
CAT16HP58SM	181151	Aço, Spring Aço	Pregalvanized, nVent CADDY Armour	25 mm	690mm ²	20

Número de catálogo	Número do artigo	Material	Acabamento	Diâmetro	Area	Cable Capacity, Cat 5e
CAT16HP912SM	181152	Aço, Spring Aço	Pregalvanized, nVent CADDY Armour	25 mm	690mm ²	20
CAT16HP24SM	181098	Aço, Spring Aço	Pregalvanized, nVent CADDY Armour	25 mm	690mm ²	20
CAT21HP24SM	181197	Aço, Spring Aço	Pregalvanized, nVent CADDY Armour	33.3 mm	1174mm ²	50
CAT21HP912SM	181199	Aço, Spring Aço	Pregalvanized, nVent CADDY Armour	33.3 mm	1174mm ²	50
CAT21HP58SM	181198	Aço, Spring Aço	Pregalvanized, nVent CADDY Armour	33.3 mm	1174mm ²	50
CAT32HP58SM	181154	Aço, Spring Aço	Pregalvanized, nVent CADDY Armour	50 mm	2561mm ²	90
CAT32HP24SM	181099	Aço, Spring Aço	Pregalvanized, nVent CADDY Armour	50 mm	2561mm ²	90
CAT32HP912SM	181155	Aço, Spring Aço	Pregalvanized, nVent CADDY Armour	50 mm	2561mm ²	90
CAT48HP24SM	181207	Aço, Spring Aço	Pregalvanized, nVent CADDY Armour	75 mm	5974mm ²	200
CAT48HP912SM	181158	Aço, Spring Aço	Pregalvanized, nVent CADDY Armour	75 mm	5974mm ²	200
CAT48HP58SM	181157	Aço, Spring Aço	Pregalvanized, nVent CADDY Armour	75 mm	5974mm ²	200
CAT64HP24SM	181208	Aço, Spring Aço	Pregalvanized, nVent CADDY Armour	100 mm	9987mm ²	330
CAT64HP58SM	181161	Aço, Spring Aço	Pregalvanized, nVent CADDY Armour	100 mm	9987mm ²	330
CAT64HP912SM	181162	Aço, Spring Aço	Pregalvanized, nVent CADDY Armour	100 mm	9987mm ²	330

Table 2/2

Número de catálogo	Número do artigo	Cable Capacity, Cat 6	Cable Capacity, Cat 6A	Espessura do flange	Static Load
CAT16HP58SM	181151	15	10	8 - 14 mm	270N
CAT16HP912SM	181152	15	10	14 - 20 mm	270N
CAT16HP24SM	181098	15	10	3 - 8 mm	270N
CAT21HP24SM	181197	40	25	3 - 8 mm	270N
CAT21HP912SM	181199	40	25	14 - 20 mm	270N
CAT21HP58SM	181198	40	25	8 - 14 mm	270N
CAT32HP58SM	181154	60	35	8 - 14 mm	270N
CAT32HP24SM	181099	60	35	3 - 8 mm	270N

Número de catálogo	Número do artigo	Cable Capacity, Cat6	Cable Capacity, Cat6A	Espessura do flange	Static Load
CAT32HP912SM	181155	60	35	14 - 20 mm	270N
CAT48HP24SM	181207	150	80	3 - 8 mm	270N
CAT48HP912SM	181158	150	80	14 - 20 mm	270N
CAT48HP58SM	181157	150	80	8 - 14 mm	270N
CAT64HP24SM	181208	220	140	3 - 8 mm	270N
CAT64HP58SM	181161	220	140	8 - 14 mm	270N
CAT64HP912SM	181162	220	140	14 - 20 mm	270N

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

América do Norte

+1 800 753 9221
Opção 1 – Apoio ao cliente
Opção 2 – Assistência
técnica

Europa

Países Baixos:
+31 800-0200135
França:
+33 800 901 793

Europa

Alemanha:
800 1890272
Outros países:
+31 13 5835404

APAC

Xangai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



O nosso forte portefólio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

