

Horizontal Rail, Front, Type R-KD, Rugged, Short Lip, 20 HP



Combinations of horizontal rails and side panels

*+ can be combined, - = combinations not recommended

	Light rail	Standard rail	Rugged rail	Rugged rail with lip
Standard rail	-	+	+	+
Standard rail with lip	+	+	+	+
Rugged rail	+	+	-	-
Rugged rail with lip	+	+	-	-

Light rail = L, Standard rail = S, Rugged rail = R, Rugged rail with lip = RL

NÚMERO DE CATÁLOGO

34566-220

The rugged horizontal rail type can handle shock and vibration up to 25 g.

CARACTERÍSTICAS

Type R-KD "rugged" horizontal rail with 3-hole fixing for increased robustness

Aluminum extrusion, anodized finish, conductive contact surface, with HP markings



CARATERÍSTICAS DO PRODUTO

Rack Width: 20HP

Quantidade por embalagem: 1

Acabamento: Anodized

Length: 106.68mm

Material: Alumínio

Família de produtos: EuropacPRO

Product Type: Horizontal Rail

Tipo: Rugged, KD

Works With: Sub racks

Net Weight: 0.068kg

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

DETALHES ADICIONAIS DO PRODUTO

Without M4 thread to front, without printing and without notch for 19" bracket.

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



O nosso forte portefólio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE