

Rack Safety Plus, 3 U, 230 / 400 V AC

The nVent SCHROFF Rack Safety Plus unit is a 19" power distribution unit used to supply AC mains power to electrical or electronic devices as a central power switch. In addition it is equipped with an emergency stop function.

CARACTERÍSTICAS

19", 3 U Power Distribution Unit with Emergency Stop function

Supplies AC mains power to electrical or electronic devices as a central power switch

400 V 3-phase or 230 V 1-phase mains input with mains fuses

AC outputs with different connector types, switched by ON/OFF switch

Permanent AC Outputs (Service)

All outputs are protected by circuit breakers

The emergency stop function meets the requirements of EN 60947-5-1 and EN 60204-1 and is vandalism-proof

An additional external emergency stop push button can be connected to the system



Function:	Emergency Stop
Works With:	Varistar CP; Novastar
Accessory Type:	Power distribution accessories
Residual Current Device:	Sim



ESPECIFICAÇÕES

Table 1/2

Número de catálogo	Product Type	Tensão de entrada AC	Número de fases	EMC Filter	Surge Arrester	Inrush Current Limiter
21270-010	Power Distributor	230V	1	Não	Sim	Sim
21270-011	Power Distributor	230V	1	Não	Não	Não
21270-005	Power Distributor	230V	1	Não	Sim	Não

Número de catálogo	Product Type	Tensão de entrada AC	Número de fases	EMC Filter	Surge Arrester	Inrush Current Limiter
21270-003	Power Distributor	230V	1	Não	Não	Não
21270-012	Power Distributor	400V	3	Não	Não	Não
21270-001	Power Distributor	400V	3	Sim	Sim	Sim

Table 2/2				
Número de catálogo	Circuit Breaker Cover	Rack Height	Tipo de soquete	Quantidade por embalagem
21270-010	Sim	3U	IEC C13	1
21270-011	Não	3U	SCHUKO, IEC C13	1
21270-005	Sim	3U	SCHUKO	1
21270-003	Não	3U	IEC C13	1
21270-012	Não	3U	IEC C13, IEC C13 LOCK	1
21270-001	Sim	3U	SCHUKO, IEC C13	1

DETALHES ADICIONAIS DO PRODUTO

For exact configuration of optional features and example configuration please refer to the item(s) delivered table.

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



O nosso forte portfólio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE