

Varistar CP LHX+ Cabinet, 10 KW, RAL 7021, EMC, 42 U, 2100H, 600W, 1000D

Obsolete

NÚMERO DE CATÁLOGO

10630-053

Varistar CP LHX + liquid cooled cabinets are designed to deliver localized energy efficient cooling to the equipment in installations where the ambient air is not filtered or temperature controlled. It incorporates an LHX5 / LHX10 cooler fitted in the bottom directly on the 19" uprights. Warm air is pulled from the rear plenum of the cabinet, cooled in the air / liquid heat exchanger, and supplied into the front plenum. The sealed cabinet assures no air is exchanged with the ambient and the noise emissions remain at a low level.

CARACTERÍSTICAS

Cabinet with integrated LHX + 19" in rack cooler, cooling capacity of up to 10 kW with temperature accuracy of $\Delta 0.1$ °K or °C

Cooling unit mounted on the 19" upright at the bottom and controller at the top. This leaves 35 U usable space

Gaskets reduce noise as low as 50.4 dB(A) at 0.2 m distance and pulling of ambient air into the cabinet

Enclosures with effective cable ducting with minimal effect on IP and EMC performance

All monitoring and managing functions can be remotely operated

Max. static load capacity 1600 kg

CARATERÍSTICAS DO PRODUTO

Rack Height: 42U

Altura: 2100mm

Frame Color: Black Grey

Largura: 600mm

Frame Color Code: RAL 7021

Cladding Material: Aço

Profundidade: 1000mm

Cladding Color: Black Grey

Quantidade por embalagem: 1

Cladding Color Code: RAL 7021

Em conformidade com: IEC 60529; IEC 61587-1; IEC 60297-3-100; IEC 61587-1

Acabamento: Pintura electrostática com Acabamento Texturado

Frame Material: Aço

Material: Aço

Família de produtos: Varistar CP

Product Type: Cabinet

Grau de proteção: IP55

Static Load: 1600kg

Net Weight: 196.6kg

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



O nosso forte portefólio de marcas:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE