

EuropacPRO 19" Subrack Kit for Backplane, Heavy, Retrofit Shielding, Front Handle

Non-EMC shielded subrack for backplane mounting, heavy version with tox welded side panels and front handle.

CARACTERISTICAS

Subrack with side panel type H ("Heavy"), 19" bracket is firmly fixed to side panel (tox-cold welded)

Supplied as space-saving flat-pack

Rear horizontal rail for backplane mounting with insulation strip

Horizontal rail type "Heavy"

Shock and Vibration resistance up to 5 g


IP 20, in accordance with IEC 60529

Shock and vibration tested to the German "Bahn" standards BN 411002, BN 411003

Internal and external dimensions in accordance with: IEC 60297-3-100, -101, IEEE 1101.1

Installed load up to 15 kg

Version with front handles



Material: Alumínio
Acabamento: Anodized; Passivated
EMC Shielding: Não
Product Type: Subrack/Chassis



ESPECIFICAÇÕES

Table 1/2

Número de catálogo	Rack Height	Profundidade	Quantidade por embalagem	For Mounting	Board Depth	Gasket Type
24567-161	3U	175mm	1	Backplane	160mm	Stainless Steel EMC
24567-163	3U	295mm	1	Backplane	160mm, 220mm, 280mm	Stainless Steel EMC
24567-164	3U	355mm	1	Backplane	160mm, 220mm, 280mm, 340mm	Stainless Steel EMC

Número de catálogo	Rack Height	Profundidade	Quantidade por embalagem	For Mounting	Board Depth	Gasket Type
24567-464	6U	355mm	1	Backplane	160mm, 220mm, 280mm, 340mm	Stainless Steel EMC
24567-461	6U	175mm	1	Backplane	160mm	Stainless Steel EMC
24567-162	3U	235mm	1	Backplane	160mm, 220mm	Stainless Steel EMC
24567-462	6U	235mm	1	Backplane	160mm, 220mm	Stainless Steel EMC
24567-463	6U	295mm	1	Backplane	160mm, 220mm, 280mm	Stainless Steel EMC

Table 2/2							
Número de catálogo	Shock and Vibration Tolerance	Inclui alça	Instalação	Em conformidade com	Rack Width	Static Load	Certifications
24567-161	5g (force)	Sim	Rack	IEC 60297-3-103	84HP	15kg	RoHS
24567-163	5g (force)	Sim	Rack	IEC 60297-3-103	84HP	15kg	RoHS, DB
24567-164	5g (force)	Sim	Rack	IEC 60297-3-103	84HP	15kg	RoHS, DB
24567-464	5g (force)	Sim	Rack	IEC 60297-3-103	84HP	15kg	DB, RoHS
24567-461	5g (force)	Sim	Rack	IEC 60297-3-103	84HP	15kg	DB, RoHS
24567-162	5g (force)	Sim	Rack	IEC 60297-3-103	84HP	15kg	RoHS, DB
24567-462	5g (force)	Sim	Rack	IEC 60297-3-103	84HP	15kg	DB, RoHS
24567-463	5g (force)	Sim	Rack	IEC 60297-3-103	84HP	15kg	DB, RoHS

DETALHES ADICIONAIS DO PRODUTO

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



O nosso forte portefólio de marcas:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE