

EuropacPRO Advanced EMC Side Panel Cover


Aluminium Side panel 3mm to increase the EMC shielding effect of the subrack by covering the not needed cut-outs.

CARACTERÍSTICAS

Side panel covers for increased lateral RF shielding

Assembled on the outside of the standard side panel

Assembly material included



Material:	Aluminio
Família de produtos:	EuropacPRO
Acabamento:	Passivated
Product Type:	Side Panel
Works With:	Subracks
Tipo:	Type H
EMC Shielding:	Sim



ESPECIFICAÇÕES

Table 1/2

Número de catálogo	Rack Height	Profundidade	Quantidade por embalagem	Length	Unidade de embalagem
24563-256	3U	235mm	2	235mm	Pair
24563-268	4U	355mm	2	355mm	Pair
24563-257	3U	275mm	2	275mm	Pair
24563-269	4U	415mm	2	415mm	Pair
24563-267	4U	295mm	2	295mm	Pair
24563-266	4U	235mm	2	235mm	Pair
24563-270	4U	495mm	2	495mm	Pair
24563-265	4U	175mm	2	175mm	Pair
24563-275	6U	175mm	2	175mm	Pair
24563-258	3U	277.75mm	2	277.75mm	Pair
24563-276	6U	235mm	2	235mm	Pair
24563-262	3U	495mm	2	495mm	Pair
24563-277	6U	275mm	2	275mm	Pair

Número de catálogo	Rack Height	Profundidade	Quantidade por embalagem	Length	Unidade de embalagem
24563-261	3U	415mm	2	415mm	Pair
24563-278	6U	277.75mm	2	277.75mm	Pair
24563-279	6U	295mm	2	295mm	Pair
24563-260	3U	355mm	2	355mm	Pair
24563-280	6U	355mm	2	355mm	Pair
24563-281	6U	415mm	2	415mm	Pair
24563-259	3U	295mm	2	295mm	Pair

Table 2/2

Número de catálogo	Rack Height	Profundidade	Quantidade por embalagem	Length	Unidade de embalagem
24563-282	6U	495mm	2	495mm	Pair
24563-255	3U	175mm	2	175mm	Pair

DETALHES ADICIONAIS DO PRODUTO

Side panel and 19" bracket are tox-cold welded together. toxen = Clinching technique, without add aids. This takes place with special tools and high pressure.

9 U version available on request.

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



O nosso forte portefólio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE