

Fence Clamp, One Conductor



The nVent ERICO Fence Clamp, One Conductor provides a secure and reliable grounding and bonding connection point for fence posts and gate structures, which is crucial for protecting equipment and personnel from electrical hazards. Engineered for durability and long-term performance, this specific clamp for a single conductor ensures system integrity in various industrial, commercial, and utility applications. Its versatile design and corrosion-resistant materials offer a dependable solution, simplifying installation while providing a lasting, maintenance-friendly connection that upholds the safety and resilience of your grounding infrastructure.

CARACTERISTICI

Specifically designed for a single conductor connection

Offers a theft-deterrent appearance for enhanced security

Includes robust stainless steel or silicone bronze hardware for superior strength and longevity

Made from high quality copper alloy that minimizes the risk of corrosion while ensuring reliable conductivity

Versatile design accepts the conductor placement either parallel or at right angles to the pipe or post

Material: Bronze;Stainless Steel 304 (EN 1.4301)

Finish: Tinned

SPECIFICAȚII


Număr de catalog	Article Number	Fence Post Size, Nominal	Fence Post Outside Diameter, Actual (Ø)	Conductor Size	nVent ERICO Cu-Bond Conductor	Complies With
FC074	198402	1 1/2"	48 mm	2/0 Solid - 250 kcmil Stranded, 50 mm ² Stranded - 120 mm ² Stranded		
FC075	198403	2"	60 mm	#4 Solid - 2/0 Stranded, 16 mm ² Stranded - 70 mm ² Stranded	CBSC8	IEC® 62561-1
FC076	198404	2"	60 mm	2/0 Solid - 250 kcmil Stranded, 50 mm ² Stranded - 120 mm ² Stranded	CBSC10, CBSC13	IEC® 62561-1

Număr de catalog	Article Number	Fence Post Size, Nominal	Fence Post Outside Diameter, Actual (Ø)	Conductor Size	nVent ERICO Cu-Bond Conductor	Complies With
FC082	198411	3 1/2"	102 mm	2/0 Solid - 250 kcmil Stranded, 50 mm ² Stranded - 120 mm ² Stranded		
FC078	198406	2 1/2"	73 mm	2/0 Solid - 250 kcmil Stranded, 16 mm ² Stranded - 120 mm ² Stranded		
FC079	198407	3"	89 mm	#4 Solid - 2/0 Stranded, 16 mm ² Stranded - 70 mm ² Stranded		

DETALII SUPLIMENTARE DESPRE PRODUS

IEC compliance is valid only for nVent ERICO Cu-Bond Conductors listed.

DIAGRAMS



AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răni corporale grave și moarte și/sau poate anula garanția dvs.

⚠ WARNING: This product can expose you to chemicals including lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Portofoliul nostru puternic de mărci:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE