

Universal Clamp, Solid Round Conductor



CARACTERISTICI

For parallel connections of nVent ERICO Cu-Bond Round Conductor



SPECIFICAȚII

Număr de catalog	Material	Depth (D)	Width (W)	nVent ERICO Cu-Bond Conductor	Unit Weight	Complies With
LPC466B	Brass	31.7mm	63.5 mm	CBSC10, CBSC13	0.28 kg	IEC® 62561-1

DETALII SUPLIMENTARE DESPRE PRODUS

IEC compliance is valid only for nVent ERICO Cu-Bond Conductors listed.

DIAGRAMS



AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

⚠ WARNING: This product can expose you to chemicals including lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE