

# Hazardous Location Hole Seals



Hazardous Location Hole Seals are designed to be used on Increased Safety (Ex e) enclosures in ATEX or IECEx Zone 1 or 2 hazardous areas. Certified to be used on metallic, non-painted enclosures, these hole seals ensure a dust-, oil- and water-tight seal. Designed to seal extra pushbutton holes, conduit openings and knockout openings, these self-centering hole seals are easy to install.

## STANDARDE INDUSTRIALE

UL 508A Component Recognized; Type 4, 4X, 12, 3R; File No. E61997

cUR Component Recognized per CSA C22.2 No. 94; Type 4, 4X, 12,

3R; File No. 42186

IECEx and ATEX Approvals

Suitable for use on increased safety enclosures for ZONE 1 or ZONE

2 assemblies

ATEX Directive 94/9/EC

ATEX

Ex e IIC Gb

Ex tb IIIC Db IP 66

Sira 14ATEX3233U

IECEx

Ex e IIC Gb

Ex tb IIIC Db IP 66

IECEx SIR 14.0073U

NEMA/EEMAC Type 3R, 4, 4X, 12

IEC 60529, IP66

## CARACTERISTICI

Secure sealing with silicon rubber gasket to protect against water and dust ingress in extreme temperature applications ranging from -55 C (-67 F) to 180 C (356 F)

Seal pushbutton holes, conduit openings and knockout openings against dust, dirt, oil and water

Easy installation in enclosure cutouts with self-centering hole seals

Hole seals are available in metric and english standard hole sizes

**Finish:** Lustruit  
**Material:** Oțel Inoxidabil 316L

## SPECIFICAȚII

| Număr de catalog | Hole Diameter | Assembly Diameter | Thread Size |
|------------------|---------------|-------------------|-------------|
| EXAS050SS6       | 20mm          | 35mm              | M20         |
| EXAS075SS6       | 25mm          | 43mm              | M25         |
| EXAS100SS6       | 32mm          | 48mm              | M32         |
| EXAS125SS6       | 40mm          | 59mm              | M40         |
| EXAS150SS6       | 50mm          | 67mm              | M50         |
| EXAS200SS6       | 63mm          | 80mm              | M63         |
| EXAS250SS6       | 75mm          | 93mm              | M75         |

## AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe [www.nvent.com](http://www.nvent.com) și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.



Portofoliul nostru puternic de mărci:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**