

19" Assembly Kit M6



For standard grounding use a grounding nut and washer on at least one attachment point.

When 19" assembly kit is used with conductive 19" panel mount, grounding cage nuts are not needed.

CARACTERISTICI

Assembly kits for assembly of 19" components into a cabinet

For mounting of front panels, distribution fields or other components on the frame, slide mounts or depth members with square cut-outs

Product Type: Assembly Kit
Finish: Oțel Zincat



SPECIFICAȚII

Table 1/2

Număr de catalog	Length	Package Quantity	Thread Size	Material	Product Family	Type
21120-196	16mm	4	M6	Oțel		Mounting Kit, Grounding
21190-095		4	M6	Oțel, ABS	RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Comptec, Inpac, MultipacPRO, Varistar CP, Eurorack, Outdoor	Mounting Kit
21120-213		4	M6	Oțel		Mounting Kit
21100-435		8	M6	Oțel, ABS	RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Comptec, Inpac, MultipacPRO, Varistar CP, Novastar, Eurorack, Outdoor	Mounting Kit
21120-199	13mm	100	M6	Oțel		Mounting Kit, Grounding

Număr de catalog	Length	Package Quantity	Thread Size	Material	Product Family	Type
21120-197	16mm	32	M6	Oțel		Mounting Kit, Grounding
21120-198	16mm	50	M6	Oțel		Mounting Kit, Grounding
21190-435		32	M6	Oțel, ABS	RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Comptec, Inpac, MultipacPRO, Varistar CP, Eurorack, Outdoor	Mounting Kit
21101-810		100	M6	Oțel, ABS	RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Comptec, Inpac, MultipacPRO, Varistar CP, Novastar, Eurorack, Outdoor	Mounting Kit
21101-809		50	M6	Oțel, ABS	RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Comptec, Inpac, MultipacPRO, Varistar CP, Novastar, Eurorack, Outdoor	Mounting Kit
21120-215		32	M6	Oțel		Mounting Kit
21120-214		50	M6	Oțel		Mounting Kit
21120-216		100	M6	Oțel		Mounting Kit

Table 2/2

Număr de catalog	Works With	Certifications
21120-196	Front Panels, Eurorack, Novastar, Varistar, Varistar CP	
21190-095	19" Cases, 19" Wallmount, 19" Indoor Cabinets, 19" Outdoor Cabinets	RoHS
21120-213	Front Panels, Eurorack, Novastar, Varistar, Varistar CP	
21100-435	19" Cases, 19" Wallmount, 19" Indoor Cabinets, 19" Outdoor Cabinets	RoHS
21120-199	Front Panels, Eurorack, Novastar, Varistar, Varistar CP	
21120-197	Front Panels, Eurorack, Novastar, Varistar, Varistar CP	
21120-198	Front Panels, Eurorack, Novastar, Varistar, Varistar CP	
21190-435	19" Cases, 19" Wallmount, 19" Indoor Cabinets, 19" Outdoor Cabinets	RoHS
21101-810	19" Cases, 19" Wallmount, 19" Indoor Cabinets, 19" Outdoor Cabinets	RoHS
21101-809	19" Cases, 19" Wallmount, 19" Indoor Cabinets, 19" Outdoor Cabinets	RoHS
21120-215	Front Panels, Eurorack, Novastar, Varistar, Varistar CP	
21120-214	Front Panels, Eurorack, Novastar, Varistar, Varistar CP	
21120-216	Front Panels, Eurorack, Novastar, Varistar, Varistar CP	

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE