

Collar Screw, Knurled Head Short Version



Integrated load spreading, replaces separate washer.
Improved joint consistency (less variation from washer misalignment) Better vibration resistance, especially with serrated collars

CARACTERISTICI

For assembly of partial width front panels

For EuropacPRO and RatiopacPRO

Knurled head for manual screwing / unscrewing

Works With: Front Panels
Type: Screw
Product Type: Screw



SPECIFICAȚII

Table 1/2

Număr de catalog	Length	Material	Finish	Package Quantity	Thread Size	Depth
21101-749	12.3mm	Brass, Lead Free	Nickel Plated	100	M2.5	18.3mm
21101-106	11mm	Oțel			M2.5	
21100-268	11mm	Brass	Nickel Plated	100	M2.5	

Table 2/2

Număr de catalog	Height	Width	Torque	Certifications
21101-749	8mm	8mm	0.3N·m	RoHS
21101-106				
21100-268				

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O

instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE