

# DC Fan

Axial fan, 119 mm, with DC input. Replacement part for 1 U fan trays.

## CARACTERISTICI

Axial 119 mm DC fan, with plug for connection cable



## SPECIFICAȚII

Table 1/2

| Număr de catalog | Works With    | Width | Length | Height | Voltage DC | Airflow |
|------------------|---------------|-------|--------|--------|------------|---------|
| 60713-600        | 19" Fan Trays | 119mm | 119mm  | 32mm   | 12V        | 140m³/h |
| 20713-242        | 19" Fan Trays | 119mm | 119mm  | 38mm   | 48V        | 184m³/h |
| 20713-241        | 19" Fan Trays | 119mm | 119mm  | 38mm   | 12V        | 184m³/h |
| 20713-240        | 19" Fan Trays | 119mm | 119mm  | 38mm   | 24V        | 184m³/h |
| 20713-172        | 19" Fan Trays | 119mm | 119mm  | 25.5mm | 24V        | 171m³/h |

Table 2/2

| Număr de catalog | Noise Level | Power | Max Static Pressure | Ambient Temperature | Package Quantity |
|------------------|-------------|-------|---------------------|---------------------|------------------|
| 60713-600        | 39dB(A)     | 8W    | 46Pa                | 70°C                | 1                |
| 20713-242        | 42dB(A)     | 8W    | 68Pa                | 70°C                | 1                |
| 20713-241        | 42dB(A)     | 8W    | 68Pa                | 70°C                | 1                |
| 20713-240        | 42dB(A)     | 8W    | 68Pa                | 70°C                | 1                |
| 20713-172        | 50.5dB(A)   | 7W    | 50.5Pa              | 70°C                | 1                |

## DETALII SUPLIMENTARE DESPRE PRODUS

Please order connection cable and protective grille separately.

## AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe [www.nvent.com](http://www.nvent.com) și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Portofoliul nostru puternic de mărci:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**