

# EuropacPRO 19" Subrack Kit for Backplane, Retrofit Shielding

Non-shielded subrack for backplane mounting.



## CARACTERISTICI

Subrack with side panel type F ("flexible"), front 19" bracket included, depth-adjustable 19" bracket sold separately (not included in items delivered)

Rear horizontal rail for backplane mounting with insulation strip

Aluminum construction

IP 20, in accordance with IEC 60529

Modifications such as cutouts, different finishes or dimensions available

Supplied as space-saving flat-pack

Horizontal rail type "light"

Internal and external dimensions in accordance with: IEC 60297-3-100, -101, IEEE 1101.1

|                       |                      |
|-----------------------|----------------------|
| <b>Finish:</b>        | Anodized; Passivated |
| <b>EMC Shielding:</b> | No                   |
| <b>Product Type:</b>  | Subrack/Chassis      |



## SPECIFICAȚII

Table 1/2

| Număr de catalog | Rack Height | Depth | Package Quantity | For Mounting | Board Depth                | Gasket Type                         |
|------------------|-------------|-------|------------------|--------------|----------------------------|-------------------------------------|
| 24563-132        | 3U          | 235mm | 1                | Backplane    | 160mm, 220mm               | Stainless Steel EMC (retrofittable) |
| 24563-133        | 3U          | 295mm | 1                | Backplane    | 160mm, 220mm, 280mm        | Stainless Steel EMC (retrofittable) |
| 24563-134        | 3U          | 355mm | 1                | Backplane    | 160mm, 220mm, 280mm, 340mm | Stainless Steel EMC (retrofittable) |
| 24563-135        | 3U          | 415mm | 1                | Backplane    | 160mm, 220mm, 280mm, 340mm | Stainless Steel EMC (retrofittable) |
| 24563-136        | 3U          | 475mm | 1                | Backplane    | 160mm, 220mm, 280mm, 340mm | Stainless Steel EMC (retrofittable) |
| 24563-431        | 6U          | 175mm | 1                | Backplane    | 160mm                      | Stainless Steel EMC (retrofittable) |
| 24563-432        | 6U          | 235mm | 1                | Backplane    | 160mm, 220mm               | Stainless Steel EMC (retrofittable) |
| 24563-433        | 6U          | 295mm | 1                | Backplane    | 160mm, 220mm, 280mm        | Stainless Steel EMC (retrofittable) |
| 24563-434        | 6U          | 355mm | 1                | Backplane    | 160mm, 220mm, 280mm, 340mm | Stainless Steel EMC (retrofittable) |
| 24563-435        | 6U          | 415mm | 1                | Backplane    | 160mm, 220mm, 280mm, 340mm | Stainless Steel EMC (retrofittable) |
| 24563-131        | 3U          | 175mm | 1                | Backplane    | 160mm                      | Stainless Steel EMC (retrofittable) |
| 24563-436        | 6U          | 475mm | 1                | Backplane    | 160mm, 220mm, 280mm, 340mm | Stainless Steel EMC (retrofittable) |

Table 2/2

| Număr de catalog | Handle Included | Mounting | Complies With   | Material | Rack Width | Static Load |
|------------------|-----------------|----------|-----------------|----------|------------|-------------|
| 24563-132        | No              | Rack     | IEC 60297-3-103 | Aluminiu | 84HP       | 11kg        |
| 24563-133        | No              | Rack     | IEC 60297-3-103 | Aluminiu | 84HP       | 11kg        |
| 24563-134        | No              | Rack     | IEC 60297-3-103 | Aluminiu | 84HP       | 11kg        |
| 24563-135        | No              | Rack     | IEC 60297-3-103 | Aluminiu | 84HP       | 11kg        |
| 24563-136        | No              | Rack     | IEC 60297-3-103 | Aluminiu | 84HP       | 11kg        |
| 24563-431        | No              | Rack     | IEC 60297-3-103 | Aluminiu | 84HP       | 11kg        |
| 24563-432        | No              | Rack     | IEC 60297-3-103 | Aluminiu | 84HP       | 11kg        |
| 24563-433        | No              | Rack     | IEC 60297-3-103 | Aluminiu | 84HP       | 11kg        |
| 24563-434        | No              | Rack     | IEC 60297-3-103 | Aluminiu | 84HP       | 11kg        |
| 24563-435        | No              | Rack     | IEC 60297-3-103 | Aluminiu | 84HP       | 11kg        |
| 24563-131        | No              | Rack     | IEC 60297-3-103 | Aluminiu | 84HP       | 11kg        |

| Număr de catalog | Handle Included | Mounting | Complies With   | Material | Rack Width | Static Load |
|------------------|-----------------|----------|-----------------|----------|------------|-------------|
| 24563-436        | No              | Rack     | IEC 60297-3-103 | Aluminiu | 84HP       | 11kg        |

## DETALII SUPLIMENTARE DESPRE PRODUS

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

## AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe [www.nvent.com](http://www.nvent.com) și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Portofoliul nostru puternic de mărci:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**