

LHX+ Fan Tray

CARACTERISTICI

LHX+ Fan trays allow for easy and hot swappable replacement of fans



Product Type: Fan Tray

SPECIFICAȚII

Table 1/2

Număr de catalog	Height	Width	Depth	Works With	Package Quantity	Airflow Direction
29714-025	244.24mm	215.15mm	126.3mm	Varistar, Varistar CP	1	Front to Top
29714-026	244.24mm	443.4mm	126.3mm	Varistar, Varistar CP	1	Front to Top

Table 2/2

Număr de catalog	Color	Color Code	Fan Quantity	Finish	Input Voltage AC	Material
29714-025	Light Grey	RAL 7035	1	Aluminum-Zinc Plated	230V	Oțel
29714-026	Light Grey	RAL 7035	1	Aluminum-Zinc Plated	230V	Oțel

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Portofoliul nostru puternic de mărci:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE