

# Mounting Kit for Telescopic Slide



Cabinet Mounting Kit for Telescopic Slide for the assembly of 2 Economy 1 U telescopic slides.

## CARACTERISTICI

For the assembly of 2 Economy 1 U telescopic slides

**Product Type:** Mounting Kit  
**Material:** Oțel  
**Finish:** Oțel Zincat



## SPECIFICAȚII

| Număr de catalog | Type            | Package Quantity | Rack Height |
|------------------|-----------------|------------------|-------------|
| 21120-165        | Heavy Universal | 1                | 2U          |
| 21120-158        | Universal       | 1                | 2U          |
| 21120-159        | Universal       | 1                | 2U          |
| 21120-160        | Universal       | 1                | 2U          |
| 21120-163        | Slim Universal  | 1                | 2U          |
| 21120-164        | Heavy Universal | 1                | 2U          |
| 21120-162        | Slim Universal  | 1                | 2U          |
| 21120-166        | Heavy Universal | 1                | 2U          |
| 21120-193        | Narrow          | 1                | 2U          |
| 21120-194        | Narrow          | 1                | 2U          |
| 21120-161        | Universal       | 1                | 2U          |

## DETALII SUPLIMENTARE DESPRE PRODUS

To mount on 19" plane please order assembly kit separately. Universal telescopic rails can also be fitted without additional components in non-standard applications, thus also in other than 19" cabinets.

## AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe [www.nvent.com](http://www.nvent.com) și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Portofoliul nostru puternic de mărci:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**