

PMC Mezzanine Front Panel, Untreated, With EMC Shielding



Mezzanine front panel is fitted into PMC front panel cut-outs. Available in different treatments. For O-ring EMC gasket.

CARACTERISTICI

Mezzanine front panel is fitted into PMC front panel cut-outs

EMC shielding with conductive O-ring

Product Type: Front Panel
Type: Front Panel without Handle
EMC Shielding: Yes



SPECIFICAȚII

Table 1/2

Număr de catalog	Package Quantity	Accessory Type	Mounting	Gasket Type	Front Finish	Rear Finish
20835-598	1	Front panel	Screw-on Front	O-Ring EMC	Anodized	Conductive
20835-922	1		Screw-on Front		Chrome Plated	Chrome Plated
20835-890	1		Screw-on Front			
20835-923	1		Screw-on Front		Chrome Plated	Chrome Plated
20835-889	1	Front panel	Screw-on Front	O-Ring EMC	Anodized	Conductive
20835-893	10		Screw-on Front		Chrome Plated	Chrome Plated
20835-928	10		Screw-on Front		Anodized	Conductive
20835-924	10		Screw-on Front		Chrome Plated	Chrome Plated

Table 2/2

Număr de catalog	Treated Edges	Complies With	Depth	Finish	Height	Material	Width
20835-598	No	PMC Mezzanine, IEEE P1386	2.5mm	Anodized	74mm	Aluminiu	12.7mm
20835-922	Yes	PMC Mezzanine, IEEE P1386			74mm	Zinc	12.7mm
20835-890	No	PMC Mezzanine, IEEE P1386			74mm	Zinc	12.7mm
20835-923	Yes	PMC Mezzanine, IEEE P1386			74mm	Zinc	12.7mm
20835-889	No	PMC Mezzanine, IEEE P1386	2.5mm	Anodized	74mm	Aluminiu	12.7mm
20835-893	Yes	PMC Mezzanine, IEEE P1386			74mm	Zinc	12.7mm
20835-928	No	PMC Mezzanine, IEEE P1386			74mm	Zinc	12.7mm
20835-924	Yes	PMC Mezzanine, IEEE P1386			74mm	Zinc	12.7mm

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Portofoliul nostru puternic de mărci:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE