


Quick Release Fastener



1/4 rotary lock with defined stop.

CARACTERISTICI

1/4 rotary lock with defined stop

Identification of locking position due to slot position

Vibration and shake proof

Qty 100 pieces

Works With: Front Panels
Product Type: Hardware Kit
Finish: Nickel Plated
Material: Oțel; Zinc Alloy; Thermoplastic



SPECIFICAȚII

Număr de catalog	Color	Package Quantity	Color Code	Depth	Height	Width	Fastener Type
21101-850	Jet Black	100	RAL 9005	20.6mm	6mm	7mm	Knurled, Slotted Head
21101-847	Pebble Grey	100	RAL 7032	16.7mm	6mm	7mm	Slotted Head
21101-849	Pebble Grey	100	RAL 7032	20.6mm	6mm	7mm	Knurled, Slotted Head
21101-848	Jet Black	100	RAL 9005	16.7mm	6mm	7mm	Slotted Head

DETALII SUPLIMENTARE DESPRE PRODUS

Quick-release fasteners: mounting without threaded inserts.

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răni corporale grave și moarte și/sau poate anula garanția dvs.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Portofoliul nostru puternic de mărci:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE