

RatiopacPRO/-Air Tip-up Handle

Tip-up carrying handles.

CARACTERISTICI

Adjustable in 30° increments

Retrofittable without mechanical tooling on case

Static load-carrying capacity 30 kg

The handle enable a user to have a better view to the front side of the case in case of desktop usage

Material:	Aluminiu; ABS
Works With:	Cases
Product Type:	Handle
Product Family:	RatiopacPRO; RatiopacPRO AIR



SPECIFICAȚII

Număr de catalog	Rack Width	Package Quantity	Handle Type	Color	Finish
24571-320	42HP	1	Tip-up Handle	Silver	Vopsit Pulbere
24571-322	84HP	1	Tip-up Handle	Silver	Vopsit Pulbere
24571-321	63HP	1	Tip-up Handle	Silver	Vopsit Pulbere

DETALII SUPLIMENTARE DESPRE PRODUS

Cannot be used in conjunction with front handles.

Assembly kit is required for tip-up carrying handle, please order separately.

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răni corporale grave și moarte și/sau poate anula garanția dvs.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Portofoliul nostru puternic de mărci:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE