

PSU 19-tums AC/DC för MicroTCA, med hantering (PM EMMC), dubbel fullstor

KATALOGNUMMER

11098-547



MTCA PSU 600 är en exceptionellt effektiv effektmodul (PM) för MicroTCA-applikationer. Det här nätaggregatet på 600 W är det mest effektiva som finns i fullformat med dubbel bredd. Den här PM:s integrerade styrenhet gör den idealisk för användning i komplexa kommunikationssystem som kör den senaste generationens processorer och ett ökat antal AMC-moduler. MTCA PSU 600 ger den effekt som krävs för 12 AMCS, 2 kylaggregat (CUS) och 2 MicroTCA Carrier Nav (MCH).

DESIGN

Dubbel höjd full-size bredd



PRODUKTATTRIBUT

Produkttyp: Strömförsörjning

Typ: 19-tums frekvensomvandlarläge

Fungerar med: MicroTCA-system

Ingångsspänning AC: 90 – 264V

Effekt: 600W

Antal utgångsspänningar: 2

Spänning 1: 12V

Ström 1: 6.8A

Spänning 2: 3.3V

Ström 2: 0.18A

Rackbredd: 6HP

Djup: 186.65mm

Höjd: 148.3mm

Nettovikt: 1.315kg

Antal i förpackningen: 1

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

YTTERLIGARE PRODUKTINFORMATION

Utdata för ta = 25 ... 55 oC med forcerad kylning på 20 cfm.

VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vårt starka utbud av varumärken:

CADDY **ERICO** **HOFFMAN** **ILSCO** **SCHROFF** **TRACHTE**