

Rack Safety Plus, 3 U, 230 V AC, C20, C13/C19

KATALOGNUMMER

21270-003

nVent SCHROFFS racksäkerhetsenhet är en 19-tums strömförsörjningsenhet som används för att förse elektriska eller elektroniska enheter med växelström som en central strömbrytare. Dessutom är den utrustad med en nödstoppsfunktion.



DESIGN

19", 3 U strömfördelningsenhet med nödstoppsfunktion

Levererar nätström till elektriska eller elektroniska enheter som en central strömbrytare

400 V 3-fas eller 230 V 1-fas nätingång med nätsäkringar

AC-utgångar med olika kontaktyper, kopplade med PÅ/AV-brytare

Permanent AC-utgångar (service)

Alla utgångar skyddas av strömbrytare

Nödstoppsfunktionen uppfyller kraven i en 60947-5-1 och en 60204-1 och är vandaliseringssäker

En extra extern nödstoppsknapp kan anslutas till systemet



PRODUKTATTRIBUT

Produkttyp: Eldistributör

Fungerar med: Varistar CP; Novastar

Funktion: Nödstopp

Ingångsspänning AC: 230V

Antal faser: 1

EMC-filer: Nej

Avledare: Nej

Inkopplingsströmsbegränsare: Nej

Restströmsenhet: Ja

Kretsbrytarkåpa: Nej

Rackhöjd: 3U

Uttagstyp: IEC C13

Tillbehörstyp: Eldistributionstillbehör

Nettovikt: 12kg

Antal i förpackningen: 1

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

YTTERLIGARE PRODUKTINFORMATION

För exakt konfiguration av tillvalsfunktioner och exempel på konfiguration, se tabellen för de artiklar som levereras.

VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vårt starka utbud av varumärken:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE