

VPX-bakplan, 3 U, 7 kortplatser, BKP3-CEN07-15,2.3-4, RTM

KATALOGNUMMER

23001-815

nVent SCHROFFS VPX-bakplan har utmärkt signalintegritet för högsta dataöverföringshastigheter.

DESIGN

I enlighet med VITA 46,0 VPX-basstandard; VITA 46,3 Serial RapidIO på VPX; VITA 46,4 PCI Express på VPX Fabric-kontakt; VITA 46,7 Ethernet på VPX Fabric-kontakt; VITA 46,11-systemhantering för VPX

DIP-omkopplare för inställningar av systemplats

JTAG-anlutningar

Låsbara aux Utility- och SENSE-kontakter

M4 strömuttag för strömförsörjning, max. 22 A per uttag för varje spänning



PRODUKTATTRIBUT

Produkttyp: Bakplan

Antal fack: 7

Rackhöjd: 3U

Bakplanstyp: VPX, VITA 65

Fackbredd: 5HP

Kontakttyp: MultiGig

Typ av strömkontakt: Kraftbultar, M4

Typ av verktygsanslutning: Microfit, 8-stifts

Bredd: 186.46mm

Bruttovikt: 0.74kg

Antal i förpackningen: 1

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail

price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

YTTERLIGARE PRODUKTINFORMATION

Andra VPX-bakplan och anpassade VPX-bakplan kan beställas.

VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vårt starka utbud av varumärken:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE