

Styrenhet för LHX+ 5 KW och 10 KW

KATALOGNUMMER

23130-668



Styrenheten berikar LHX+. Den ansluts till LHX+-givarna och den motoriserade kylmedelsventilen 23130-607. Detta gör det möjligt för kylaren att reglera kylvätskans luftflöde baserat på en börvärde för kylningsluftens (tilluftstemperatur) temperatur. Den ger avancerad fjärrövervakningsfunktionalitet och olika inställningsfunktioner.

DESIGN

Reglering av kylvätskeflödet baserat på börvärdet för kylluftens temperatur (tilluft). Fler kontrollfunktioner med vattenkontrollpaket

Separat, kompakt 19"-styrenhet utan lösa kablar i den övre skåpsektionen

Tydligt markerade plug & play-sensoranslutningar

PRODUKTATTRIBUT

Höjd: 88mm

Djup: 220mm

Fungerar med: Varistar; Varistar CP

Antal i förpackningen: 1

Färg: Svartgrå

Färgkod: RAL 7021

Yta: Aluminium-zinkpläterad

Ingångsspänning AC: 230V

Material: Stål

Produktfamilj: Varistar CP

Produkttyp: Reglerenhet

Rackhöjd: 2U

Bredd: 439.5mm

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on

SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

YTTERLIGARE PRODUKTINFORMATION

Extern display som tillval.

VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vårt starka utbud av varumärken:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE