

EuropacPRO täckplatta, Universal, 84 HP, 415 mm

KATALOGNUMMER

24560-055

En täckplatta används för elektromagnetisk avskärmning eller som mekaniskt skydd. Locket kan användas är icke-standardiserade brädor kommer att monteras i understället.

DESIGN

Skärmning tillhandahålls av valfria EMC-packningar av rostfritt stål, mellan täckplattan och sidopanelen

För variabel positionering av horisontella skenor, t.ex. för kretskort med icke-standardformat

Perforeringsgrad 58 %

Lämplig för användning med alla horisontella skenor



PRODUKTATTRIBUT

Rackbredd: 84HP

Djup: 415mm

Antal i förpackningen: 2

Yta: Passiverad

Material: Aluminium

Produktfamilj: EuropacPRO

Produkttyp: Täckplatta

Typ: Universell

Fungerar med: Underrack

Nettovikt: 0.693kg

Paketenhet: Par

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched

from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

YTTERLIGARE PRODUKTINFORMATION

Dessutom krävs 4 kontaktskenor per underrack för att fästa skyddet på den horisontella skenan.

VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vårt starka utbud av varumärken:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE