


CPCI PlusIO-system med pluggbart nätaggregat, 4 U, 8 kortplats



KATALOGNUMMER

24579-400

4 U CompactPCI PlusIO-system med vertikal korthållare för en CPCI PlusIO-systemstyrenhet, 4 CompactPCI och 3 CompactPCI seriella periferikort och ett CompactPCI 3 U pluggbart nätaggregat.

DESIGN

I enlighet med IEC 60297 3 101, 102, 103; IEEE 1101,1, 1101,10/11; bakplan i enlighet med PICMG 2,0 rev. 3,0 och PICMG 2,30 rev. 1,0




System med vertikal korthållare. Kortformat framsida: 3 U, 160 mm djup, 8 fack; bakre i/O: 3 U, 80 mm djup, 3 fack

Bakplan 4 kortplatser, 3 U, 32 bitar, CompactPCI; 4 kortplatser, 3 U, CompactPCI PlusIO

Värmeavledning med 1 U varmväxlingsfläkt, luftflöde nedifrån och upp

19-TUMS KOMPATIBELT NÄTAGGREGAT, 250 W, 3 U, 8 HP

Möjlighet att montera en hårddisk



PRODUKTATTRIBUT

Produkttyp: System

Antal fack: 8

Typ: 19 tum rackfäste

Bakplanstyp: 3 U, 4-facks CompactPCI och 4-facks CompactPCI, seriell

Dataöverföring: 32-bitars PCI-buss; PCIe Gen2

Effekt per fack: 40W

Ingångsspänning AC: 100 – 240V

Luftflödesriktning: Underdel till överdel



Rackhöjd: 4U

Strömförsörjningstyp: (1) PSU som är möjlig att plugga

Strömförsörjning inkluderad: Ja

Bakre I/O: Ja

Uppfyller: PICMG 2.30 R1.0

Djup: 275mm

Höjd: 177mm

Nettovikt: 10.8kg

Antal i förpackningen: 1

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

YTTERLIGARE PRODUKTINFORMATION

Modifierade system finns tillgängliga på begäran.

VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vårt starka utbud av varumärken:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE