

Horisontell skena, fram, typ R-LD, robust, lång kant , 40 hk

KATALOGNUMMER

34566-340

Den robusta horisontella skentypen kan hantera stötar och vibrationer upp till 25 g. det möjliggör användning av IEEE-handtag.

DESIGN


Robusta horisontella skenor av typ R-LD med 3-håls infästning för ökad robusthet

För insättning/extraktion av CompactPCI- eller VME64x-kort

Med HP-enheter tryckta från 28 HP och uppåt

Längd 20, 28, 40, 42, 63, 84 HP eller 1000 mm

Extrudering av aluminium, anodiserad yta, ledande kontaktyta, med HP-märkning



Combinations of horizontal rails and side panels

	Side panel	Light rail	Standard rail	Heavy rail	Robust rail
Standard rail	-	+	+	+	+
Light rail	+	+	+	+	+
Heavy rail	+	+	+	+	+
Robust rail	+	+	+	+	+

Legend: + = can be combined, - = combination not recommended

PRODUKTATTRIBUT

Rackbredd: 40HP

Antal i förpackningen: 1

Yta: Anodiserad

Längd: 208.28mm

Material: Aluminium

Produktfamilj: EuropacPRO

Produkttyp: Horisontell skena

Typ: Robust, LD

Fungerar med: Underrack

Bruttovikt: 0.131kg

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched

from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vårt starka utbud av varumärken:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE