

Horisontell skena, bak, typ R-ST, robust, Standard, 42 HP



Combinations of horizontal rails and side panels

		$\sigma^{\text{H}} = \text{can be avoided}$		$\sigma^{\text{H}} = \text{combination not recommended}$	
Support $\rightarrow$		-	+	+	+
		+	substituted for flexion for shear stress	substituted for shear stress for flexion	+
Light $\rightarrow$		substituted for light	substituted for flexion	+	+
		+	+	-	-
Horizontal end					
Side panel					
		Light $\rightarrow$ 1	Flexion $\rightarrow$ 2	Shear $\rightarrow$ 3	Plugged $\rightarrow$ 4

KATALOGNUMMER

34566-542

Den horisontella skenan, typ robust ST möjliggör isolerad montering av ett bakplan. Isoleringen görs med en isoleringsremsa.

DESIGN

Robust horisontell skena av typ R-ST med 3-hålsfäste för ökad robusthet

Extrudering av aluminium, anodiserad yta, ledande kontaktyta, med HP-märkning

Med HP-enheter tryckta från 28 HP och uppåt



PRODUKTATTRIBUT

Rackbredd: 42HP

Antal i förpackningen: 1

Yta: Anodiserad

Längd: 218.44mm

Material: Aluminium

Produktfamilij: EuropacPRO

Produkttyp: Horisontell skena

Typ: Robust, ST

Fungerar med: Underrack

Nettovikt: 0.04kg

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

YTTERLIGARE PRODUKTINFORMATION

Tänk på att leveranser kan utföras i angivna SPQ (SPQ, t.ex. 5 stycken, 10 stycken, 50 stycken, etc.). Olika orderkvantiteter (t.ex. 2 stycken) kan ändras till nästa möjliga leveranskvantitet = Standardförpackningskvantitet.

VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vårt starka utbud av varumärken:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE