nVent CADDY

We connect and protect

401 Clevis Hanger, EG, PG, 1" Pipe, 25 DN, 34 mm OD, M10 Rod

物料号

4010100EG

功能

Recommended for the suspension of stationary non-insulated pipe lines

Flared edges help prevent sharp surfaces from coming into contact with the pipe (1/2" to 2" pipe sizes)

Clevis bottom pivots to allow pipe to be fed from either direction

Conforms with Federal Specification WW-H-171 (Type 1), Manufacturers Standardization Society (MSS) SP-58 (Type 1)

产品属性

订货号: 179420

材料: 钢

完成: 电镀锌;预镀锌

管道尺寸: 1"

NB/DN: 25

外径 (OD): 34 mm

杆尺寸 (RS): M10

A: 71 mm

B: 35 mm

C: 9 mm

静态负载: 2700N

图





警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent
的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

北美

+1.800.753.9221

，按 1 转客户服务

，按 2 转技术支持

欧洲

荷兰：

+31 800-0200135

法国：

+33 800 901 793

欧洲

德国：

800 1890272

其他国家/地区：

+31 13 5835404

亚太地区

上海：

+ 86 21 2412 1618/19

悉尼：

+61 2 9751 8500

©2026 nVent。所有 nVent 标志和徽标均由 nVent Services GmbH 或其附属公司拥有或授权。所有其他商标均为其各自所有者的财产。nVent 保留更改规格的权利，恕不另行通知。

本文档由系统生成。