

LED 灯套件



LED light kits provide interior enclosure lighting suitable for remote and darkened enclosure applications. These light kits are light-weight and in a small form factor which are ideal where space is limited. The light can be mechanically fastened with included hardware to maintain enclosure UL listing (up to Type 4X), or can be magnetically attached to flat steel surfaces. The lights have auto-sensing circuitry (AC voltage 90 VAC to 265 VAC and DC voltage 20 VDC to 60 VDC). Option of a manual on/off switch or a PIR motion sensor is available.

功能

防护等级 II（双层绝缘）

400 lumen at 120-degree angle of illumination

6000-7000K color temperature

Power consumption for all models is 5 watts

The power output allows up to 10 lights to be connected to each other (daisy chain)

Input and output connectors are included (16 AWG)

Operating temperature -22 F to 140 F (-30 C to 60 C)

Life expectancy of 60,000 hours at 68 F (20 C) under specifications

技术参数

物料号	订货号	材料	完成	颜色	电源	安装
LEDD2S35	26085	塑料	平滑哑光	浅灰色	直流	螺钉
LEDD1S35	26084	塑料	平滑哑光	浅灰色	直流	螺钉
LEDA1S35	26078	塑料	平滑哑光	浅灰色	交流	螺钉

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE