

底座双侧盖板，PS



用于覆盖 PF/PV

底座侧面开口的侧板。以限制对内部的接触。

功能

Description: Side panels to cover the openings in the sides of the PF/PV plinths. Double folded panels for maximum strength. Compatible with combinable and semi-compact enclosure ranges.

Material: 1.5 mm steel plate.

Finish: RAL 7022 structured powder coating.

Pack quantity: 2 panels. Mounting accessories included with PF/PV.

厚度: 1.5mm
材料: 低碳钢
完成: 粉末涂层
颜色代码: RAL 7022
颜色: 本影灰

技术参数

物料号	订货号	高度	宽度	深度	产品系列	外壳材料
PS2100	PS2100	200mm	999mm	27mm	独立	低碳钢
PS1060	PS1060	100mm	600mm	27mm	独立	低碳钢
PS2080	PS2080	200mm	800mm	27mm	独立	低碳钢
PS1040	PS1040	100mm	400mm	27mm	独立	低碳钢
PS2050	PS2050	200mm	500mm	27mm	独立	低碳钢
PS1080	PS1080	100mm	800mm	27mm	独立	低碳钢
PS2030	PS2030	200mm	300mm	27mm	独立	低碳钢
PS1100	PS1100	100mm	999mm	27mm	独立	低碳钢
PS2040	PS2040	200mm	400mm	27mm	独立	低碳钢
PS2060	PS2060	200mm	600mm	27mm	独立	低碳钢

物料号	订货号	高度	宽度	深度	产品系列	外壳材料
PS1050	PS1050	100mm	500mm	27mm	独立	低碳钢
PS1030	PS1030	100mm	300mm	27mm	独立	低碳钢

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE