

带 P 47 连接器的 CPCI 电源背板

适用 CompactPCI 应用的电源背板。带 P47 电源连接器。

功能

符合：PICMG 2.11 R1.0 CompactPCI 电源接口技术参数

符合：PICMG 2.9 R1.0 系统管理总线技术参数

单柜, 支持并行或冗余操作

地理地址可调

通过插入到插头的压接触点供电, 背板无电源电压

电源线可作为附件提供

带有电源柱的直流插座, 电压降极低



技术参数

Table 1/2

物料号	产品类型	插槽数	机架高度	背板类型	槽宽	连接器类型
23098-393	背板	1	3U	CompactPCI 电源背板, 带 P47 插座	8HP	
23098-396	背板	1	6U	CompactPCI 电源背板, 带 P47 插座	8HP	
23098-395	背板	1	6U	CompactPCI 电源背板, 带 P47 插座	8HP	
23098-394	背板	2	3U	CompactPCI 电源背板, 带 P47 插座	8HP	P47

Table 2/2

物料号	电源连接器类型	多功能连接器类型	宽度	包装数量
23098-393	(1) P47	SMCQ, 12 针, MicroMatch, 10 针	39.6mm	1
23098-396	(2) P47	SMCQ, 12 针, MicroMatch, 10 针	39.6mm	1
23098-395	(1) P47	SMCQ, 12 针, MicroMatch, 10 针	39.6mm	1
23098-394	(2) P47	SMCQ, 12 针, MicroMatch, 10 针	80.3mm	1

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE