


水平轨道，后部，L-ST 型，重型，标准，1000 mm



Combinations of horizontal rails and side panels

„H“ = can be combined, „N“ = combination not recommended

	Horizontal rail	Horizontal rail with side panel	Horizontal rail with side panel (for CompacPRO)	Horizontal rail with side panel (for PropacPRO)
Horizontal rail	-	+	+	+
Horizontal rail with side panel	+	+	+	+
Horizontal rail with side panel (for CompacPRO)	+	+	+	+
Horizontal rail with side panel (for PropacPRO)	+	+	+	+

Side panel

Light = L, Dark = D, Heavy = H, Super = S

物料号

34560-501

ST

型水平轨道可以非接触的方式装配背板。隔离通过绝缘条实现。

功能

用于背板非接触安装，带绝缘条

符合高水平机械标准 (H-ST)

安装在插箱顶部和底部

< 28 HP 无印制

铝挤压件，阳极氧化，接触表面导电，带 HP 标记



产品属性

机架宽度: 195HP

包装数量: 1

完成: 阳极氧化

长度: 1000mm

材料: 铝

产品系列: EuropacPRO; RatiopacPRO; RatiopacPRO AIR; CompacPRO; PropacPRO

产品类型: 水平横梁

类型: 重型，ST

搭配: 插箱; 仪器箱

净重: 0.304kg

*所示价格为每件价格，不含增值税。是否含包装费和运费取决于当地情况。如果这些费用应为总价的一部分，报价中将包含包装费和运费。给定的价格为非约束性建议零售价 (RRP)，即 nVent 标价。当地经销商的最终销售价格可能会有所不同。在 SCHROFF.nVent.com 上请求或生成的报价仅对商业客户 (B2B) 有效。上面显示的交货时间是从 nVent SCHROFF 工厂发货该项目的估计值。运输时间不包括在此估计中，因为运输时间可能会有所不同，具体取决于送货地址、包裹尺寸和其他因素。对于配置的产品，在非推荐区域（“检测到的碰撞区域”）进行的开孔和修改可能会产生额外的工程和/或设计成本，这可能会增加最初的报价。

其他产品详情

以多个标准包装的形式交货。以单件为单位定价。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE