



H-VT 型水平轨道，后部，重型，20 HP



Combinations of horizontal rails and side panels

H = gap, be considered. *+* = combination not recommended

	Backpack 1.0	Backpack 1.5	Backpack 2.0	Backpack 2.5
Heavy 1.0	-	+	+	+
Heavy 1.5	+	+	+	+
Heavy 2.0	+	+	+	+
Heavy 2.5	+	+	+	+
Backpack 1.0	-	-	-	-
Backpack 1.5	-	-	-	-
Backpack 2.0	-	-	-	-
Backpack 2.5	-	-	-	-

Light 1.0, Backpack 1.0, Heavy 1.0, Backpack 1.5, Heavy 1.5, Backpack 2.0, Heavy 2.0, Backpack 2.5, Heavy 2.5

物料号

34560-720

VT 型横梁，可直接装配背板。

功能

用于直接安装背板

安装在插箱顶部和底部

嵌入式安装，适用于较高机械振动环境 (H-VT)

铝挤压件，阳极氧化，接触表面导电



产品属性

机架宽度: 20HP

包装数量: 1

完成: 阳极氧化

长度: 106.68mm

材料: 铝

产品系列: EuropacPRO; RatiopacPRO; RatiopacPRO AIR; CompacPRO; PropacPRO

产品类型: 水平横梁

类型: 重型, VT

搭配: 插箱; 仪器箱

净重: 0.036kg

*所示价格为每件价格，不含增值税。是否含包装费和运费取决于当地情况。如果这些费用应为总价的一部分，报价中将包含包装费和运费。给定的价格为非约束性建议零售价 (RRP)，即 nVent 标价。当地经销商的最终销售价格可能会有所不同。在 SCHROFF.nVent.com 上请求或生成的报价仅对商业客户 (B2B) 有效。上面显示的交货时间是从 nVent SCHROFF 工厂发货该项目的估计值。运输时间不包括在此估计中，因为运输时间可能会有所不同，具体取决于送货地址、包裹尺寸和其他因素。对于配置的产品，在非推荐区域（“检测到的碰撞区域”）进行的开孔和修改可能会产生额外的工程和/或设计成本，这可能会增加最初的报价。

其他产品详情

以多个标准包装的形式交货。以单件为单位定价。

请注意，交货数量会按照声明的标准包装量执行（例如，5 件、10 件、50 件等）我们会将不符合规定的订购数量（例如 2 件）更改为下一个可执行的标准包装量发货。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE