


盘头螺钉, Torx



盘头螺钉。

功能

盘头螺钉

类型: 盘头螺钉
产品类型: 螺钉
材料: 钢



技术参数

物料号	长度	完成	包装数量	螺纹尺寸	产品系列	搭配	扭矩
24560-148	10mm	镀镍	100	M2.5		背板, 测试适配器	0.3N • m
24560-147	7mm	镀镍	100	M2.5	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO	前面板, Eurorack, Novastar, Varistar, Varistar CP	0.3N • m
24560-161	12mm	镀镍	100	M2.5		背板, 测试适配器	0.3N • m
24560-135	6mm	镀锌	100	M4	EuropacPRO	插箱	1.3N • m
24571-372	10mm	镀锌	100	M4	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO	前面板, Eurorack, Novastar, Varistar, Varistar CP	2.4N • m

物料号	长度	完成	包装数量	螺纹尺寸	产品系列	搭配	扭矩
24571-371	14mm	镀锌	100	M4	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO	前面板, Eurorack, Novastar, Varistar, Varistar CP	2.4N • m
24560-178	6mm	镀镍	100	M2.5	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO	前面板, Eurorack, Novastar, Varistar, Varistar CP	
24560-162	14mm	镀镍	100	M2.5		背板, 测试适配器	
24560-163	16mm	镀镍	100	M2.5		背板, 测试适配器	

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE