

PCB 支架

PCB 固定块可将 PCB
固定至前面板。提供不同材料的版本。

功能

用于将 PCB 固定在前面板上

产品类型: 支架
搭配: 前面板
类型: PCB 支架



技术参数

Table 1/2

物料号	包装数量	可燃性等级	材料	深度	高度	宽度
60807-181	1		锌合金	8.6mm	11.1mm	10.2mm
60807-203	1		锌合金			
60807-183	1	UL® 94V-0	聚碳酸酯			
60807-011	1	UL® 94V-0	聚碳酸酯			
60807-211	1	UL® 94V-0	聚碳酸酯			

Table 2/2

物料号	螺纹尺寸	螺纹类型
60807-181	M2.5	公制
60807-203		
60807-183		
60807-011		
60807-211		

其他产品详情

以多个标准包装的形式交货。以单件为单位定价。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE