

# RatiopacPRO/-Air 配翻转式提手

用于 RatiopacPRO/-AIR 的折叠式把手，静态承载能力为 30 kg，无需机械工具即可改装仪器箱。



## 功能

可 30° 增量调节

无需机械工具即可改装仪器箱

静态承载能力 30 千克

对于桌面式应用，此把手有助于用户更方便地查看机箱正面

材料: 铝; ABS  
 搭配: 仪器箱  
 产品类型: 手柄  
 产品系列: RatiopacPRO; RatiopacPRO AIR



## 技术参数

| 物料号       | 机架宽度 | 包装数量 | 手柄类型  | 颜色 | 完成   |
|-----------|------|------|-------|----|------|
| 24571-320 | 42HP | 1    | 翻转式把手 | 银色 | 粉末涂层 |
| 24571-322 | 84HP | 1    | 翻转式把手 | 银色 | 粉末涂层 |
| 24571-321 | 63HP | 1    | 翻转式把手 | 银色 | 粉末涂层 |

## 其他产品详情

不能与前把手一起使用。

翻转式把手需要装配套件，请单独订购。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 [www.nvent.com](http://www.nvent.com) 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



我们强大的品牌组合:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE