

RatiopacPRO Complete Desktop Case, 屏蔽型



带 EMC 屏蔽的 nVent SCHROFF RatiopacPRO 机箱可为 19"

的独立电子组件提供电子保护。这种灵活、可靠的仪器箱可轻松从桌面式转换为 19"

机架安装仪器箱，包含四种不同的选项。本版本的机箱可为桌面式应用提供美观的设计。

功能

带预装组件的桌面式机箱, 符合 IEC 60297-3-101标准, 用于 19" 组件, 例如, 面板单元和欧式板卡

屏蔽型

此版本带遮盖条

底板带通风

后面板带通风孔

符合 DIN EN 62368-1

静态负载:	25kg
产品类型:	仪器箱
类型:	适用安装 19" 部件的仪器箱
产品系列:	RatiopacPRO
EMC 屏蔽:	是



技术参数

Table 1/3						
物料号	机架高度	机架宽度	深度	包装数量	可用高度	可用宽度
24572-065	6U	63HP	315.5mm	1	245.7mm	326mm
24572-054	3U	84HP	315.5mm	1	112.3mm	432mm
24572-055	3U	84HP	375.5mm	1	112.3mm	432mm
24572-051	3U	42HP	255.5mm	1	112.3mm	219mm
24572-056	3U	84HP	435.5mm	1	112.3mm	432mm
24572-064	6U	42HP	315.5mm	1	245.7mm	219mm
24572-053	3U	63HP	315.5mm	1	112.3mm	326mm
24572-066	6U	84HP	315.5mm	1	245.7mm	432mm
24572-067	6U	84HP	375.5mm	1	245.7mm	432mm
24572-052	3U	42HP	315.5mm	1	112.3mm	219mm
24572-050	3U	28HP	255.5mm	1	112.3mm	148mm
24572-068	6U	84HP	435.5mm	1	245.7mm	432mm

Table 2/3						
物料号	前部框架结构	制冷选项	符合	完成	高度	材料
24572-065	侧面饰件, 水平横梁	否	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	钝化, 粉末涂层	265.9m	铝
24572-054	侧面饰件, 水平横梁	否	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	钝化, 粉末涂层	132.6m	铝
24572-055	侧面饰件, 水平横梁	否	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	钝化, 粉末涂层	132.6m	铝
24572-051	侧面饰件, 水平横梁	否	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	钝化, 粉末涂层	132.6m	铝
24572-056	侧面饰件, 水平横梁	否	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	钝化, 粉末涂层	132.6m	铝
24572-064	侧面饰件, 水平横梁	否	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	钝化, 粉末涂层	265.9m	铝
24572-053	侧面饰件, 水平横梁	否	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	钝化, 粉末涂层	132.6m	铝
24572-066	侧面饰件, 水平横梁	否	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	钝化, 粉末涂层	265.9m	铝

物料号	前部框架结构	制冷选项	符合	完成	高度	材料
24572-067	侧面饰件, 水平横梁	否	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	钝化, 粉末涂层	265.9m m	铝
24572-052	侧面饰件, 水平横梁	否	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	钝化, 粉末涂层	132.6m m	铝
24572-050	侧面饰件, 水平横梁	否	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	钝化, 粉末涂层	132.6m m	铝
24572-068	侧面饰件, 水平横梁	否	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	钝化, 粉末涂层	265.9m m	铝

Table 3/3		
物料号	防护等级	宽度
24572-065	IP20	342.4mm
24572-054	IP20	448.9mm
24572-055	IP20	448.9mm
24572-051	IP20	235.5mm
24572-056	IP20	448.9mm
24572-064	IP20	235.5mm
24572-053	IP20	342.4mm
24572-066	IP20	448.9mm
24572-067	IP20	448.9mm
24572-052	IP20	235.5mm
24572-050	IP20	164.4mm
24572-068	IP20	448.9mm

其他产品详情

- 可定制（特殊颜色或尺寸）。
- 定制解决方案（支持顶盖、底板或侧面板开孔）。
- 提供装配服务，一件起售。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent

的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE