

Varistar CP Cabeling Rack



符合高静态负载要求的焊接钢框架。适合高电缆密度和 19" 集成。

功能

预配置, 立即可用型机柜

静态承载重能力高达 1600 千克

防护等级 IP 20

可安装不同类型的网络设备

集成垂直和水平电缆管理部件

可轻松集成到通道密封系统中

产品类型: 机架
材料: 钢
框架材料: 钢

技术参数

Table 1/2

物料号	机架高度	覆层材料	框架颜色	高度	框架颜色代码	覆层颜色
10630-027	42U	钢	暗灰色	2000mm	RAL 7021	暗灰色
10630-028	42U	钢	暗灰色	2000mm	RAL 7021	暗灰色

Table 2/2

物料号	宽度	深度	静态负载	覆层颜色代码	包装数量	动态荷载	完成
10630-027	800mm	1200mm	1600kg	RAL 7021	1	1000kgf	粉末涂层
10630-028	800mm	1200mm	1600kg	RAL 7021	1	1000kgf	粉末涂层

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE