

# H2Omit 通风排水阀



H2Omit Vent Drains allow accumulated water to drain out the bottom of an enclosure. The UL-approved vent drains also function as an air pressure equalizer, reducing the harmful effects of temperature-induced vacuums that could pull water and moisture into the enclosure.

## 工业标准

UL 508A Listed; Type 4, 4X; File No. E61997

cUL Listed per CSA C22.2 No 94; Type 4, 4X; File No. E61997

IEC 60529, IPx6

NEMA/EMAC Type 4, 4X

IEC 60529, IPx6

## 功能

使用重力排出收集的液体

压力均衡后，单向机械切断可防止水和污染物进入机柜

有助于减少腐蚀，延长内部电气和电子元件寿命。

安装在低碳钢、铝、不锈钢或非金属机柜的底部

正确安装可以保持机柜UL防护等级

不锈钢通风排水阀

非金属通风排水阀

耐腐蚀聚酯材料

Installs in a 7/8-inch hole in the bottom of enclosure with provided nut or in a 1/2-inch NPT/NPS threaded conduit hub

Corrosion-resistant polyester material with a Type 304 stainless steel sleeve

2.00-inch long x 1.25-inch outside diameter

技术参数

| 物料号      | 订货号   | 高度   | 宽度   | 深度   | 材料      | 完成 |
|----------|-------|------|------|------|---------|----|
| AVDR4SS4 | 17764 | 67mm | 35mm | 35mm | 不锈钢 304 | 拉丝 |

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 [www.nvent.com](http://www.nvent.com) 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE