

危险场所视窗套件

Hazardous Location Window Kits are designed to be used on Increased Safety (Ex e) enclosures in ATEX or IECEx Zone 1 or 2 hazardous areas. These window kits ensure a dust-, oil-, and water-tight seal. Designed for use as viewing windows, these window kits are ideal for visibility of internal enclosure components. The windows are easily installed by making a cutout in the enclosure and attaching the window and frame with included mounting hardware.

工业标准

UL 508A Component Recognized; Type 4, 4X, 12, 3R; 文件编号 E61997

适用于 ZONE 1 或 ZONE 2 元件的增安型机柜

Suitable for use on increased safety enclosures for ZONE 1 or ZONE 2 assemblies

ATEX Directive 94/9/EC

ATEX

Sira 13ATEX3315U

Ex e IIC Gb

Ex tb IIIC Db IP 66

IECEx

IECEx SIR 13.0123U

Ex e IIC Gb

Ex tb IIIC Db IP 66

cUR Component Recognized per CSA C22.2 No. 94; Type 4, 4X, 12,

3R; File No. E61997

NEMA/EEMAC 4, 4X, 12, 13

IEC 60529, IP66



功能

硅垫片保证紧密密封，防止高温应用中的水和粉尘侵入

使用窗框架五金件轻松安装到机柜开孔

Maintain visual on components through .25-in. (6-mm) tempered safety glass

完成: 拉丝

材料: 不锈钢 316L

技术参数

物料号	订货号	厚度	开孔尺寸
EXWK53SS6	27021	1.98mm	170 x 119mm
EXWK95SS6	27022	1.98mm	272 x 183mm
EXWK138SS6	27024	1.98mm	373 x 246mm

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE