

卫生设计接线盒，HDTB



The nVent HOFFMAN Hygienic Design Terminal Box, HDTB range, is specially engineered to protect critical equipment in high sanitary environments and for ease of cleaning. With self-draining, smooth-finished surfaces, gap-free design and high protection degree, the enclosure minimizes hygiene risks and helps reduce downtime to increase productivity.

工业标准

cULus_UL Listed

CE, UK CA, UL

功能

Material: AISI 304L pre-grained stainless steel. Body and cover: 1.5 mm.

Body: Folded and seam welded. Four M6x13 studs for bottom profile / mounting plate fixation.

Cover: Folded and seam welded. Sides sloped at 3°. AISI 316 HD bolts with blue silicone gasket included.

Gasket: A one piece removable silicone gasket with molded corners helps ensure proper sealing, and makes removing and replacing it faster and easier for cleaning and maintenance operations. The silicone is FDA 21 CFR 177.2600 compliant. Colour blue (RAL 5010).

Cable access: No gland openings as standard to minimize hygiene risks.

Earthing: M8x18 mm earthing studs in body and cover, M8 nuts, earthing washers and earthing labels.

Protection: Corresponds with IP 66/69 | TYPE 4X, 13 | IK08.

Finish: 400 pre-grained stainless steel, polished to Ra < 0.8 µm.

Delivery: Body with cover and mounting accessories.

Additional information: For accessories on the outside of the enclosure, please see our HD accessories section.

厚度: 1.5mm

完成: 拉丝

材料: 不锈钢 304L

技术参数

物料号	高度	宽度	深度
HDTB202012	200mm	199mm	120mm
HDTB304012	300mm	400mm	120mm
HDTB204012	200mm	400mm	120mm
HDTB151508	150mm	150mm	80mm
HDTB151512	150mm	150mm	120mm
HDTB203012	200mm	299mm	120mm

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合：

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE