

内门，ADI

内门为标准或玻璃前门后面的设备提供可转动的安装表面，可覆盖其他元器件，并防止未经授权的操作。

功能



Description: For controls, meters, lamps, etc. Hinges can be mounted to allow left or right hand opening. Lock double-bit 3 mm insert; 700 mm high doors and above have 2 locks. Usable depth between inner and external door: 35 mm. Adjustable depth position with AMG accessory. Workable area: H-55, W- 108. 19" version available on request. Machining is required for stainless steel enclosures.

Material: Door 1.5 mm mild steel, vertical top and bottom profiles 2 mm mild steel.

Finish: RAL 7035 structured powder coating.

Protection: IP 2XC.

Pack quantity: Inner door, two vertical profiles, top and bottom profiles and mounting accessories.

厚度: 1.5mm
颜色: 浅灰色
材料: 低碳钢
完成: 粉末涂层
颜色代码: RAL 7035

技术参数

物料号	订货号	高度	宽度	深度	门尺寸	门锁数量
ADI06050R5	ADI06050R5	574mm	461mm	71mm	545 x 392mm	1
ADI04040R5	ADI04040R5	374mm	374mm	71mm	345 x 292mm	1
ADI06040R5	ADI06040R5	574mm	374mm	71mm	545 x 292mm	1
ADI05050R5	ADI05050R5	474mm	461mm	71mm	445 x 392mm	1
ADI04050R5	ADI04050R5	374mm	461mm	71mm	345 x 392mm	1

物料号	订货号	高度	宽度	深度	门尺寸	门锁数量
ADI06080R5	ADI06080R5	574mm	761mm	71mm	545 x 692mm	1
ADI05040R5	ADI05040R5	474mm	374mm	71mm	445 x 292mm	1
ADI04030R5	ADI04030R5	374mm	261mm	71mm	345 x 192mm	1
ADI05030R5	ADI05030R5	474mm	261mm	71mm	445 x 192mm	1
ADI04060R5	ADI04060R5	374mm	561mm	71mm	345 x 492mm	1
ADI06060R5	ADI06060R5	574mm	561mm	71mm	545 x 492mm	1
ADI08060R5	ADI08060R5	774mm	561mm	71mm	745 x 492mm	2
ADI08080R5	ADI08080R5	774mm	761mm	71mm	745 x 692mm	2
ADI10080R5	ADI10080R5	974mm	761mm	71mm	945 x 692mm	2
ADI08040R5	ADI08040R5	774mm	374mm	71mm	745 x 292mm	2
ADI10060R5	ADI10060R5	974mm	561mm	71mm	945 x 492mm	2
ADI07050R5	ADI07050R5	674mm	461mm	71mm	645 x 392mm	2
ADI12060R5	ADI12060R5	1174mm	561mm	71mm	1145 x 492mm	2
ADI12080R5	ADI12080R5	1174mm	761mm	71mm	1145 x 692mm	2

其他产品详情

Not suitable for AFS.

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE