# 吊环，LE

这些吊环可确保安全地运输和取放机柜。

## 功能

Description: Mounts directly to the frame corner pieces of the enclosure for when lifting operations are required. Complies with DIN 580 lifting requirements. M12 thread.

Maximum load: 3400N per lifting eye with max angle of 45°. Please follow nVent HOFFMAN lifting instructions.

Pack quantity: 4 pieces.

## 技术参数

| 物料号 | 订货号 | 高度 | 宽度 | 深度 | 材料 | 完成 |
|---|---|---|---|---|---|---|
| LE9304 | LE9304 | 71mm | 50mm | 30mm | 低碳钢 | 镀锌 |
| LE9304SS | LE9304SS | 71mm | 50mm | 30mm | 不锈钢 304 | 研磨 |
| LE9316SS | | 71mm | 50mm | 30mm | 不锈钢 316L | 研磨 |

## 警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2026 nVent。所有 nVent 标志和徽标均由 nVent Services GmbH 或其附属公司拥有或授权。所有其他商标均为其各自所有者的财产。nVent 保留更改规格的权利，恕不另行通知。

本文档由系统生成。