

安装板，MP

钢制安装板有助于加快机柜组装速度（因为可以轻松加工并配备组件，然后再进行安装）。

功能

Description: Standard mounting plate. It can also be mounted on the side of an enclosure by using MPS kit or slid in from the side with the MTS profile. For heavy loads in vibrating environments use mounting plate reinforcement profile MPR and MPE or MPEF brackets.

Material: 3 mm galvanized steel.

Pack quantity: 1 piece.

Maximum load: 6000 N.

Mounting requirements: Use MPA for mounting the MP inside the enclosure. Adjustable in depth with MPD accessory.



厚度: 3mm
完成: 镀锌
材料: 低碳钢

技术参数

Table 1/2

物料号	订货号	高度	宽度	深度	安装板高度	安装板高度
MP1412		1400mm	1200mm	25mm	50.94mm	1294mm
MP1206		1200mm	600mm	25mm	43.07mm	1094mm
MP2014		1894mm	1294mm	25mm	74.57mm	1894mm
MP2210	MP2210	2200mm	1000mm	25mm	82.44mm	2094mm
MP1806	MP1806	1800mm	600mm	25mm	66.7mm	1694mm
MP1816	MP1816	1800mm	1600mm	25mm	66.7mm	1694mm
MP2208	MP2208	2200mm	800mm	25mm	82.44mm	2094mm

物料号	订货号	高度	宽度	深度	安装板高度	安装板高度
MP1805	MP1805	1800mm	500mm	25mm	66.7mm	1694mm
MP1808	MP1808	1800mm	800mm	25mm	66.7mm	1694mm
MP2010	MP2010	2000mm	1000mm	25mm	74.56mm	1894mm
MP1812	MP1812	1800mm	1200mm	25mm	66.7mm	1694mm
MP2005	MP2005	2000mm	500mm	25mm	74.56mm	1894mm
MP1208		1200mm	800mm	25mm	43.07mm	1094mm
MP2006	MP2006	2000mm	600mm	25mm	74.56mm	1894mm
MP1406		1400mm	600mm	25mm	50.94mm	1294mm
MP1810	MP1810	1800mm	1000mm	25mm	66.7mm	1694mm
MP1612		1600mm	1200mm	25mm	58.82mm	1494mm
MP2008	MP2008	2000mm	800mm	25mm	74.56mm	1894mm
MP2004	MP2004	2000mm	400mm	25mm	74.56mm	1894mm
MP1408		1400mm	800mm	25mm	50.94mm	1294mm

Table 2/2

物料号	订货号	高度	宽度	深度	安装板高度	安装板高度
MP1410		1400mm	1000mm	25mm	50.94mm	1294mm
MP1610		1600mm	1000mm	25mm	58.82mm	1494mm
MP1212		1200mm	1200mm	25mm	43.07mm	1094mm
MP2206	MP2206	2200mm	600mm	25mm	82.44mm	2094mm
MP2212	MP2212	2200mm	1200mm	25mm	82.44mm	2094mm
MP1606		1600mm	600mm	25mm	58.81mm	1494mm
MP1804	MP1804	1800mm	400mm	25mm	66.7mm	1694mm
MP2016	MP2016	2000mm	1600mm	25mm	74.56mm	1894mm
MP1608		1600mm	800mm	25mm	58.82mm	1494mm
MP2012	MP2012	2000mm	1200mm	25mm	74.56mm	1894mm

其他产品详情

Note: for 1600 mm width, the mounting plate is delivered as two 800 mm width mounting plates and one filler plate.

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE